

NEW PRODUCT DATA SHEET

PAGlink Micro Charger

ULTRA-COMPACT GOLD MOUNT TRAVEL CHARGER



- The world's smallest, single-position, multi-battery Gold Mount charger.
- Charge up to 4 PAGlink Gold Mount batteries linked.
- Designed for light travel - fits easily in your camera bag.
- Compatible with PAG Gold Mount Li-Ion batteries.
- Charges two fully discharged 94Wh PAGlink batteries in 8 hours.
- Power from a PSU (100-240V AC), a 12V vehicle battery or a 2A USB charger.

DESCRIPTION

The PAGlink Micro Charger is ideal when you want to travel light and charge PAGlink Gold Mount batteries. This ultra-compact, inexpensive charger is small enough to fit in any camera bag. It accepts 5-20V DC input, and can be powered from a variety of sources, making it the ideal travel charger.

The Micro Charger will charge PAGlink Gold Mount batteries of any rated capacity, and from any state of charge, individually or linked. It can also be used for charging non-linking Gold Mount Li-Ion batteries manufactured by PAG.

PAGlink is the first camera battery system that allows batteries to be linked for charging. At the end of a shoot, simply link your batteries and connect them to the charger. The next day, they will be fully charged and ready to go, without intervention.

If you need power in a hurry, one fully discharged 94Wh battery will be 80% charged in approximately 3 hours. Two fully-discharged 94Wh PAGlink batteries will be fully-charged in approximately 8 hours.

The charge status of each battery is shown on its individual display. The most-discharged batteries are given priority until all the batteries are in a similar state of charge; they are then fully-charged simultaneously.

The charger features LED indication of charging, charge completion, an absent battery and a faulty battery.

The Micro Charger can be powered using the Power Supply Unit included, which accepts 100-240V AC input, converted to



CHARGER



AC POWER SUPPLY UNIT



USB POWER LEAD



IN-CAR POWER LEAD

low-voltage DC. A power plug of your choice is included, which is interchangeable with other options that enable direct connection to worldwide AC outlets.

The charger can also be powered from a 12V vehicle battery, via the dashboard lighter socket, or a USB charger (2A) using the DC power leads included.

SPECIFICATION

PAGlink Micro Charger Model 9713

Suitable Batteries:

Individual or linked charging, from any state of charge:
PAGlink Gold Mount Batteries Models 9306 & 9313.

Individual charging only:

PAG Gold Mount Batteries Models 9310A, 9305A.

PAGlink Charging:

The Micro Charger is designed for charging simultaneously up to 4 linked PAGlink batteries, of any rated capacity, from any state of charge.

Recovery Charge:

Automatically recovers a Li-Ion battery after shut down.

Input: DC 5V to 20V (2A). Connector: 2.1mm DC (PP90).
Power Supply Unit: AC 100-240V ~ autoselected. Frequency 50-60 Hz. Maximum power consumption 35W.

Output: 1.5 Amps.

Operating Temperature Range:

0°C to 40°C (+32°F to +104°F).

Dimensions (charging shoe only) L x W x H:

2.8" x 2.5" x 1.3" (72 x 63 x 33mm).

Weight: 2.6oz (75g).

Typical Battery Charging Times:

1	94Wh battery:	4hrs
2	94Wh batteries:	8hrs
3	94Wh batteries:	12hrs
4	94W batteries:	16hrs

Times are for fully-discharged batteries to fully-charged, when powering the charger using the Power Supply Unit. Charge times will be less if batteries are partially discharged. 150Wh batteries will take 50% longer.



PAG Ltd.
565 Kingston Road
London SW20 8SA

E sales@paguk.com
T +44 (0)20 8543 3131
www.paguk.com

©OCT 2017 PAG Ltd. PAG is the trademark of PAG Ltd.
PAG reserves the right to change the specifications contained herein without notice